

# Styli and accessories

When precision matters, insist on genuine Renishaw styli. Don't settle for less!

## M2 threaded stylus range

Ruby ball styli				Silicon nitride and zirconia ball styli				Key A Ball diameter B Overall length Dimensions in mm (in)												
(stainless steel)	(tungsten carbide)	(ceramic)	(carbon fibre)	(stainless steel)	(tungsten carbide)	(stainless steel)	(tungsten carbide)													
A-5000-7802 A 1.5 (0.06) B 10.0 (0.40)	A-5000-4154 A 4.0 (0.16) B 10.0 (0.40)	A-5000-4156 A 6.0 (0.24) B 10.0 (0.40)	A-5000-7805 A 0.5 (0.020) B 10.0 (0.40)	A-5003-0577 A 0.7 (0.028) B 20.0 (0.79)	A-5003-0034 A 1.5 (0.06) B 20.0 (0.79)	A-5003-0938 A 3.0 (0.12) B 20.0 (0.79)	A-5003-0043 A 4.0 (0.16) B 30.0 (1.19)	A-5003-1370 A 4.0 (0.16) B 30.0 (1.19)	A-5003-4779 A 5.0 (0.20) B 30.0 (1.19)	A-5003-4780 A 6.0 (0.24) B 30.0 (1.19)	A-5003-0066 A 5.0 (0.20) B 50.0 (1.97)	A-5003-4241 A 4.0 (0.16) B 30.0 (1.19)	A-5003-2286 A 5.0 (0.20) B 50.0 (1.97)	A-5003-4785 A 5.0 (0.20) B 75.0 (2.96)	A-5003-4786 A 6.0 (0.24) B 75.0 (2.96)	A-5003-2291 A 6.0 (0.24) B 100.0 (3.94)	A-5003-6120 A 2.0 (0.08) B 10.0 (0.40)	A-5003-7723 A 2.0 (0.08) B 10.0 (0.40)	A-5004-1017 A 2.0 (0.08) B 20.0 (0.79)	A-5004-2923 A 2.0 (0.08) B 20.0 (0.79)
Star styli fixed				Star styli centres		Special purpose styli		Spherically ended styli				Disc styli								
(stainless steel)				(tungsten carbide)		(stainless steel)		(tungsten carbide)				(silver steel)								
A-5000-7811 A 1.0 (0.04) B 10.0 (0.40)	A-5003-4788 A 1.0 (0.04) B 20.0 (0.79)	A-5000-7629 A 2.0 (0.08) B 18.0 (0.71)	A-5000-3626 A 2.0 (0.08) B 30.0 (1.19)	A-5003-4789 A 1.0 (0.04) B 8.5 (0.34)	A-5000-3609 A 2.0 (0.08) B 16.5 (0.65)	A-5004-7588 A 18.0 (0.71) B 15.0 (0.60)	A-5000-3614 A 18.0 (0.71) B 11.0 (0.44)	A-5003-0074 A 2.0 (0.08) B 40.0 (1.58)	A-5000-3611 A 6.0 (0.24) B 1.2 (0.05)	A-5000-7809 A 18.0 (0.71) B 1.5 (0.06)										

## M3 threaded stylus range

REVO recommended styli				Cylinder styli				Stylus extensions														
(stainless steel)	(tungsten carbide)	(ceramic)	(carbon fibre)	(silver steel)	(ruby)	(stainless steel)	(carbon fibre)	(stainless steel)	(carbon fibre)	(ceramic)	(carbon fibre)	(carbon fibre)	(carbon fibre)									
A-5000-7806 A 1.0 (0.04) B 10.0 (0.40)	A-5000-7807 A 2.0 (0.08) B 10.0 (0.40)	A-5000-3604 A 3.0 (0.12) B 10.0 (0.40)	A-5000-4154 A 4.0 (0.16) B 10.0 (0.40)	A-5003-0033 A 1.0 (0.04) B 20.0 (0.79)	A-5000-8663 A 1.0 (0.04) B 27.5 (1.08)	A-5004-3404 A 2.0 (0.08) B 30.0 (1.19)	A-5003-4177 A 3.0 (0.12) B 30.0 (1.19)	A-5003-7852 A 3.0 (0.12) B 30.0 (1.19)	A-5003-3877 A 3.0 (0.12) B 40.0 (1.58)	A-5004-7589 A 1.5 (0.06) B 11.0 (0.44)	A-5004-7590 A 3.0 (0.12) B 13.0 (0.52)	A-5000-8877 A 1.5 (0.06) B 15.0 (0.60)	A-5000-7812 A 2.0 (0.08) B 20.0 (0.79)	A-5003-0073 A 4.0 (0.16) B 20.0 (0.79)	A-5004-7610 A 5.0 (0.20) B 5.0 (0.20)	A-5004-7585 A 10.0 (0.40) B 10.0 (0.40)	A-5004-7586 A 20.0 (0.79) B 20.0 (0.79)	A-5004-7611 A 40.0 (1.58) B 40.0 (1.58)	A-5003-0070 A 30.0 (1.19) B 30.0 (1.19)	A-5003-0072 A 50.0 (1.97) B 50.0 (1.97)	A-5003-2280 A 40.0 (1.58) B 40.0 (1.58)	A-5003-2283 A 90.0 (3.55) B 90.0 (3.55)

## M4 threaded stylus range

Ruby ball styli				Silicon nitride ball styli				Zirconia ball styli		Stylus extensions				Disc and hollow ball styli					
(stainless steel)	(carbon fibre)	(tungsten carbide)	(tungsten carbide)	(stainless steel)	(ceramic)	(stainless steel)	(ceramic)	(stainless steel)	(carbon fibre)	(stainless steel)	(carbon fibre)	(ceramic)	(carbon fibre)	(silver steel)	(ceramic)				
A-5000-3551 A 1.0 (0.04) B 21.0 (0.83)	A-5000-3552 A 2.0 (0.08) B 21.0 (0.83)	A-5000-3553 A 3.0 (0.12) B 21.0 (0.83)	A-5000-7606 A 4.0 (0.16) B 21.0 (0.83)	A-5003-3554 A 4.0 (0.16) B 20.0 (0.79)	A-5003-4880 A 6.0 (0.24) B 27.5 (1.08)	A-5003-4882 A 8.0 (0.32) B 75.0 (2.96)	A-5003-4881 A 6.0 (0.24) B 100.0 (3.94)	A-5003-4883 A 8.0 (0.32) B 100.0 (3.94)	A-5003-5723 A 2.0 (0.08) B 21.0 (0.83)	A-5003-5725 A 4.0 (0.16) B 75.0 (2.96)	A-5003-5737 A 4.0 (0.16) B 21.0 (0.83)	A-5003-5740 A 6.0 (0.24) B 75.0 (2.96)	A-5004-7609 A 10.0 (0.40) B 10.0 (0.40)	A-5004-7583 A 20.0 (0.79) B 20.0 (0.79)	A-5004-7584 A 35.0 (1.38) B 35.0 (1.38)	A-5003-0075 A 50.0 (1.97) B 50.0 (1.97)	A-5004-4864 A 75.0 (2.96) B 75.0 (2.96)	A-5000-7612 A 35.0 (1.38) B 5.0 (0.20)	A-5000-7814 A 30.0 (1.19) B 17.0 (0.67)

## M5 threaded stylus range

Stylus extensions				Ruby ball styli				Hemispherical styli				Disc styli		Knuckles, cubes and bolts				Ruby micro ball styli														
(carbon fibre)	(carbon fibre)	(tungsten carbide)	(tungsten carbide)	(ceramic)	(stainless steel)	(silver steel)	(ceramic)	(stainless steel)	(carbon fibre)	(stainless steel)	(carbon fibre)	(carbon fibre)	(carbon fibre)	(carbon fibre)	(carbon fibre)	(carbon fibre)	(carbon fibre)	(carbon fibre)	(tungsten carbide)	(tungsten carbide)	(tungsten carbide)											
A-5555-0662 B 180.0 (7.09)	A-5003-5251 A 8.0 (0.32) B 75.0 (2.96)	A-5003-5262 A 8.0 (0.32) B 100.0 (3.94)	A-5003-5265 A 6.0 (0.24) B 150.0 (5.91)	A-5003-5269 A 8.0 (0.32) B 200.0 (7.88)	A-5003-5204 A 1.0 (0.04) B 20.0 (0.79)	A-5003-5218 A 3.0 (0.12) B 30.0 (1.19)	A-5003-5224 A 3.0 (0.12) B 40.0 (1.58)	A-5003-5236 A 5.0 (0.20) B 50.0 (1.97)	A-5003-4472 A 6.0 (0.24) B 100.0 (3.94)	A-5004-6463 A 2.0 (0.08) B 80.0 (3.15)	A-5004-6470 A 6.0 (0.24) B 100.0 (3.94)	A-5004-6467 A 2.0 (0.08) B 80.0 (3.15)	A-5003-7306 A 6.0 (0.24) B 100.0 (3.94)	A-5003-6510 A 6.0 (0.24) B 100.0 (3.94)	A-5003-1436 A 6.0 (0.24) B 50.0 (1.97)	A-5003-1358 A 6.0 (0.24) B 100.0 (3.94)	A-5004-7599 A 6.0 (0.24) B 100.0 (3.94)	A-5004-7601 A 20.0 (0.79) B 20.0 (0.79)	A-5004-7602 A 30.0 (1.19) B 30.0 (1.19)	A-5000-7754 A 30.0 (1.19) B 30.0 (1.19)	A-5000-7755 A 50.0 (1.97) B 50.0 (1.97)	A-5000-7727 A 100.0 (3.94) B 100.0 (3.94)	A-5003-5275 A 16.0 (0.63) B 19.5 (0.77)	A-5003-5277 A 30.0 (1.19) B 24.5 (0.97)	A-5003-5288 A 12.0 (0.48) B 3.0 (0.12)	A-5003-5290 A 35.0 (1.38) B 5.0 (0.20)	A-5003-5278 B 36.5 (1.44)	A-5003-5676 B 33.0 (1.30)	A-5555-0194 B 20.0 (0.79)	A-5003-5201 A 0.3 (0.012) B 20.0 (0.79)	A-5003-5227 A 0.7 (0.03) B 50.0 (1.97)	A-5003-5233 A 2.5 (0.10) B 50.0 (1.97)

## Accessories

Styli knuckles		Styli centres		Styli tools		Adaptors	
A-5000-7534 M2 thread size B 8.0 (0.32)	A-5000-7616 M3 thread size B 12.0 (0.48)	A-5000-3627 M2 thread size B 7.5 (0.30)	A-5000-7610 M3 thread size B 13.0 (0.52)	A-5003-2380 M2 carbon fibre range	A-5004-7587 M4 thread size	A-5004-7595 M4/M2 B 5.0 (0.20)	A-2054-6350 M4/O4.5 B 10.0 (0.40)

