

**Component set C (R-FSC-CC-6) 163 M6 components**

Qty.	Part no.	Description
6	R-S-910-6	Ø9 mm x 10 mm standoff
4	R-S-1310-6	Ø13 mm x 10 mm standoff
8	R-S-1320-6	Ø13 mm x 20 mm standoff
8	R-S-1325-6	Ø13 mm x 25 mm standoff
8	R-S-1350-6	Ø13 mm x 50 mm standoff
4	R-S-1910-6	Ø19 mm x 10 mm standoff
8	R-S-1920-6	Ø19 mm x 20 mm standoff
8	R-S-1925-6	Ø19 mm x 25 mm standoff
8	R-S-1950-6	Ø19 mm x 50 mm standoff
6	R-S-19100-6	Ø19 mm x 100 mm standoff
8	R-S-2520-6	Ø25 mm x 20 mm standoff
8	R-S-2525-6	Ø25 mm x 25 mm standoff
8	R-S-2550-6	Ø25 mm x 50 mm standoff
6	R-S-25100-6	Ø25 mm x 100 mm standoff
4	R-SP-1325-6	Ø13 mm x 25 mm standoff
2	R-SP-1925-6	Ø19 mm x 25 mm standoff
6	R-CT-40-30-6	40 mm tension clamp with 30 mm post
12	R-CT-64-70-6	64 mm tension clamp with 70 mm post
3	R-CT-95-83-6	95 mm tension clamp with 83 mm post
3	R-CT-100P-83-6	100 mm tension clamp plunger with 83 mm post
1	R-CTB-25-6	25 mm tension clamp bracket
6	R-ROD-6	Delrin resting cone
6	R-RPS-6	Steel resting pin
1	R-APJ-6	Adjustable pivot joint
4	R-AJ-13-6	Ø13 mm adjustable jackstand
3	R-AJ-25-6	Ø25 mm adjustable jackstand
3	R-AS-45-6	45 mm long adjustable slide
4	R-AS-70-6	70 mm long adjustable slide
2	R-TB-2025-6	Tower block with base 20 mm x 20 mm x 30 mm
1	R-T-25300-6	25 mm x 25 mm x 300 mm tower
2	R-TC-500200	500 mm x 200 mm x 25 mm component tray
2	R-BC10	50 mm x 200 mm x 150 mm compartment box (not shown)


**M6 CMM clamping kit  
with component set C**

Renishaw fixture kits include a fixture base plate and set of components



**Kit choices**

Kit part no.	Set	Base plate size
R-KC-C1C-6*	C	13 mm x 300 mm x 300 mm
R-KC-C2C-6*	C	13 mm x 450 mm x 450 mm
R-KC-C3C-6*	C	19 mm x 600 mm x 600 mm
R-KC-C4C-6**	C	19 mm x 750 mm x 750 mm
R-KC-C5C-6**	C	19 mm x 750 mm x 1000 mm
R-KC-C6C-6**	C	19 mm x 900 mm x 1200 mm



\* The kit is supplied with a pair of CMM plate clamps.

\*\* For large plates custom bolt holes are recommended to mount the plate onto the CMM table. Please provide the make and the machine model when placing an order.

For more information visit [www.renishaw.com/shop](http://www.renishaw.com/shop)

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY FOR SOLELY ARISING FROM ANY INACCURACIES IN THIS DOCUMENT.

© 2017 Renishaw plc. All rights reserved.


Renishaw and the probe symbol used in the RENISHAW logo are registered trademarks of Renishaw plc in the United Kingdom and other countries.

RENISHAW and the probe symbol used in the RENISHAW logo are registered trademarks of Renishaw plc or its subsidiaries. All other brand names and product names listed in this document are trade names, trade marks or registered trademarks of their respective owners.



H - 1 0 0 0 - 0 1 3 9 - 0 1

Issued: 01.2017 Part no. H-1000-0139-01-A



Tower  
R-T25300-6

010 mm standoff  
R-S-1010-6  
R-S-1920-6  
R-S-1925-6  
R-S-1950-6  
R-S-19100-6

025 mm standoff  
R-S-1920-6  
R-S-1925-6  
R-S-1950-6  
R-S-25100-6

013 mm standoff  
R-S-1320-6  
R-S-1325-6  
R-S-1350-6

Adjustable  
jackstand  
R-AJ-13-6

Adjustable  
pivot joint  
R-APJ-6

Adjustable  
jackstand  
R-AJ-25-6

Pin standoff  
R-SP-1925-6

Adjustable slide  
R-AS-70-6  
R-AS-45-6

Tower block  
R-TB-2530-6

019 mm x 10 mm  
standoff R-S-910-6

Tension clamp plunger  
R-CT-100P-83-6

Pin standoff  
R-MP-13-6

Tension clamp R-CT-95-83-6

Tension clamp bracket  
R-CTB-25-6

Tension clamp  
R-CT-40-30-6

Delrin® resting cone  
R-RCD-6  
Steel resting pin  
R-RSP-6

013 mm x 10 mm  
standoff  
R-S-1310-6

Tension clamp R-CT-64-70-6