


# M8 CMM magnetic and clamping kit with component set B

Renishaw fixture kits including a fixture base plate and set of components




Kit choices		
Kit part no.	Set	Base plate size
R-KC-MC1B-8*	B	13 mm × 300 mm × 300 mm
R-KC-MC2B-8*	B	13 mm × 450 mm × 450 mm
R-KC-MC3B-8*	B	19 mm × 600 mm × 600 mm
R-KC-MC4B-8**	B	19 mm × 750 mm × 750 mm
R-KC-MC5B-8**	B	19 mm × 750 mm × 1020 mm
R-KC-MC6B-8**	B	19 mm × 900 mm × 1200 mm



\* The kit is supplied with a pair of CMM plate clamps.


\*\* For large plates custom bolt holes are recommended to mount the plate to the CMM table. Please provide the make and the machine model when placing an order.



**Component set B (R-FSC-MCB-8) 114 M8 components**

Quantity	Part no.	Description
4	R-M-13-8	Ø13 mm x 25 mm magnet
4	R-M-19-8	Ø19 mm x 25 mm magnet
4	R-M-25-8	Ø25 mm x 25 mm magnet
2	R-MP-13-8	Ø13 mm x 25 mm pin magnet
3	R-S-1315-8	Ø13 mm x 15 mm standoff
6	R-S-1320-8	Ø13 mm x 20 mm standoff
6	R-S-1325-8	Ø13 mm x 25 mm standoff
6	R-S-1350-8	Ø13 mm x 50 mm standoff
3	R-S-1915-8	Ø19 mm x 15 mm standoff
6	R-S-1920-8	Ø19 mm x 20 mm standoff
6	R-S-1925-8	Ø19 mm x 25 mm standoff
6	R-S-1950-8	Ø19 mm x 50 mm standoff
4	R-S-19100-8	Ø19 mm x 100 mm standoff
6	R-S-2520-8	Ø25 mm x 20 mm standoff
6	R-S-2525-8	Ø25 mm x 25 mm standoff
6	R-S-2550-8	Ø25 mm x 50 mm standoff
4	R-S-25100-8	Ø25 mm x 50 mm standoff
4	R-CT-40-30-8	40 mm tension clamp with 30 mm post
8	R-CT-64-70-8	63.5 mm tension clamp with 68 mm post
4	R-RCD-8	13 mm x 16 mm Delrin® resting cone
4	R-RCS-8	13 mm x 16 mm steel resting cone
2	R-AJ-19-8	Ø19 mm x 37 mm adjustable jackstand
2	R-AJ-25-8	Ø25 mm x 42 mm adjustable jackstand
1	R-AS-45-8	45 mm x 10 mm long adjustable slide
3	R-AS-70-8	70 mm x 10 mm long adjustable slide
2	R-TB-2530-8	25 mm x 25 mm x 40 mm tower block with base
1	R-TC-500200	500 mm x 200 mm x 25 mm component tray
1	R-BC10	200 mm x 150 mm x 45 mm compartment box (not shown)

[www.renishaw.com/contact](http://www.renishaw.com/contact)  #renishaw

+44 (0) 1453 524111  [sfpd@renishaw.com](mailto:sfpd@renishaw.com)

© 2018–2021 Renishaw plc. All rights reserved. RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners. Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 8JR, UK. WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW. Part no.: H-1000-0147-02-A Issued: 12.2021