


M8 CMM clamping kit with component set A

Renishaw fixture kits include a fixture base plate and set of components




Kit choices

Kit part no.	Set	Base plate size
R-KC-C1A-8*	A	13 mm × 300 mm × 300 mm
R-KC-C2A-8*	A	13 mm × 450 mm × 450 mm
R-KC-C3A-8*	A	19 mm × 600 mm × 600 mm
R-KC-C4A-8**	A	19 mm × 750 mm × 750 mm
R-KC-C5A-8**	A	19 mm × 750 mm × 1020 mm
R-KC-C6A-8**	A	19 mm × 900 mm × 1200 mm



* The kit is supplied with a pair of CMM plate clamps.

** For large plates custom bolt holes are recommended to mount the plate to the CMM table. Please provide the make and the machine model when placing an order.



Component set A (R-FSC-CA-8) 43 M8 components

Qty.	Part no.	Description
3	R-S-1320-8	Ø13 mm × 20 mm standoff
3	R-S-1325-8	Ø13 mm × 25 mm standoff
3	R-S-1350-8	Ø13 mm × 50 mm standoff
3	R-S-1920-8	Ø19 mm × 20 mm standoff
3	R-S-1925-8	Ø19 mm × 25 mm standoff
3	R-S-1950-8	Ø19 mm × 50 mm standoff
3	R-S-2520-8	Ø25 mm × 20 mm standoff
3	R-S-2525-8	Ø25 mm × 25 mm standoff
3	R-S-2550-8	Ø25 mm × 50 mm standoff
2	R-SP-1325-8	Ø13 mm × 25 mm pin standoff
2	R-CT-40-30-8	40 mm tension clamp with 30 mm post
4	R-CT-64-70-8	64 mm tension clamp with 70 mm post
4	R-RCD-8	Delrin® resting cone
1	R-AJ-19-8	Ø19 mm adjustable jackstand
1	R-AS-70-8	70 mm long adjustable slide
1	R-TC-500200	500 mm × 200 mm × 25 mm component tray
1	R-BC10	50 mm × 200 mm × 150 mm compartment box (not shown)

For worldwide contact details, visit www.renishaw.com/contact

RENISHAW HAS MADE CONSIDERABLE EFFORTS TO ENSURE THE CONTENT OF THIS DOCUMENT IS CORRECT AT THE DATE OF PUBLICATION BUT MAKES NO WARRANTIES OR REPRESENTATIONS REGARDING THE CONTENT. RENISHAW EXCLUDES LIABILITY, HOWSOEVER ARISING, FOR ANY INACCURACIES IN THIS DOCUMENT.

© 2015 – 2016 Renishaw plc. All rights reserved.

Renishaw reserves the right to change specifications without notice.

RENISHAW and the probe symbol used in the RENISHAW logo are registered trade marks of Renishaw plc in the United Kingdom and other countries. apply innovation and names and designations of other Renishaw products and technologies are trade marks of Renishaw plc or its subsidiaries. All other brand names and product names used in this document are trade names, trade marks or registered trade marks of their respective owners.



H - 1000 - 0140 - 01

Issued: 03.16 Part no. H-1000-0140-01-B