

Product VTN6000 catalyst
 Revision date 22 February 2018
 Revision 1



Safety Data Sheet (SDS)

Section 1: Identification of the substance/preparation and of the company/undertaking

1.1 Product identifier

Product name VTN6000 catalyst
Synonyms, Trade names No information available.

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses Model and mould making.
Uses advised against Any other purpose.

1.3 Details of the supplier of the safety data sheet

Supplier Renishaw plc
 Brooms Road
 Stone Business Park
 Stone, Staffordshire
 ST15 0SH
 United Kingdom
 Tel: +44 (0) 1785 285000 (during UK office hours 09:00 to 17:00 UTC).
 msds@renishaw.com

Contact person

1.4 Emergency telephone number

Emergency telephone 999 / 911 or local emergency number

Section 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (EC 1272/2008)
 Physical and chemical hazards Not classified
 Human health Not classified
 Environment Not classified

2.2 Label elements

Contains Not applicable

Label in accordance with (EC) no. 1272/2008 No pictogram required

Signal word No Signal Word

Hazard statements No hazard statements required

Precautionary statements No precautionary statements required

2.3 Other hazards

None known.

Section 3: Composition/identification of ingredients

3.1 Substance

Not applicable.

3.2 Mixtures

Name	Product identifier	Reg. EU 1272/2008	%
Silicone polymer, crosslinking by addition contains hydrogen modified polysiloxane	CAS-No.: EC No.:		<100%

The full text for all hazard statements are displayed in section 16.

Composition comments

The data shown are in accordance with the latest EC Directives. There are no ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs, vPvBs or Substances of equivalent concern, or have been assigned a workplace exposure limit and hence require reporting in this section.

Section 4: First aid measures

4.1 Description of first aid measures

General information

Provide general first aid, rest, warmth and fresh air. As a general rule, in case of doubt or if symptoms persist, always call a doctor. Seek medical attention for all burns and eye injuries, regardless how minor they may seem. First aid personnel must be aware of own risk during rescue.

Inhalation

If this product is inhaled and symptoms occur, move the exposed person to fresh air promptly. If breathing is difficult, give oxygen. Seek medical attention. Keep person warm and at rest.

Ingestion

If this product is ingested, remove victim immediately from source of exposure. Rinse mouth thoroughly. Do not induce vomiting. Provide fresh air, warmth and rest, preferably in comfortable upright sitting position. Never give anything by mouth to an unconscious person. Seek medical advice (show the label where possible).

Skin contact

Wash exposed area with soap and water. Get medical attention if irritation develops or persists. Contaminated clothing should be washed before re-use.

Eye contact

Do not rub eye. If this product contacts the eyes, gently flush eyes with water for at least fifteen (15) minutes, lifting the upper and lower eyelids occasionally. Avoid contaminating unaffected eye. Remove contact lenses if present and easy to do so. Seek medical attention.

4.2 Most important symptoms and effects, both acute and delayed

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

No specific symptoms noted.

Ingestion

No specific symptoms noted.

Skin contact

No specific symptoms noted.

Eye contact

May cause temporary eye irritation.

4.3 Indication of any immediate medical attention and special treatment needed

Notes to the physician

Treat symptomatically.

Section 5: Fire-fighting measures

5.1 Extinguishing media

Extinguishing media

Use fire-extinguishing media appropriate for surrounding materials: Powder dry chemicals, carbon dioxide, foam spray.

Unsuitable extinguishing media

High volume water jet. Do not use alkaline powder extinguishing agent.

5.2 Special hazards arising from the substance or mixture

Hazardous combustion products

During fire, toxic gases (CO, CO₂) are formed. Combustion may lead to the release of hydrogen. Silica.

Unusual fire & explosion hazards

Material can accumulate static charges which may cause an electrical spark (ignition source). Use proper bonding and/or grounding procedures. Evolves hydrogen on contact with acids, alkalis, alcohols, powdered metals or metal oxides.

Specific hazards

If heated, harmful vapours may be formed. Floors may become slippery, avoid falls.

5.3 Advice for firefighters

- Special fire fighting procedures** If possible, fight fire from protected position. Use powder, dry chemical, carbon dioxide etc. for initial stage of fire. For a large scale fire, use foam to smother flames. Avoid breathing fire vapours. Ventilate closed spaces before entering them. Keep up-wind to avoid fumes. Containers close to fire should be removed immediately or cooled with water if safe to do so.
- Protective equipment for firefighters** Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

Section 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

- Personal precautions** Do not touch or walk through spilled material. Evacuate and ventilate area. Eliminate all sources of ignition. Use non-sparking hand tools and explosion proof electrical equipment. Wear protective clothing as described in Section 8 of this safety data sheet. Avoid inhalation of vapours and contact with skin and eyes. Provide adequate ventilation. In case of inadequate ventilation, use respiratory protection. Do not smoke, eat or drink while using this product. Keep unnecessary and unprotected personnel from entering.
- For emergency responders** Follow safe handling advice and personal protective equipment recommendations for normal use of product.

6.2 Environmental precautions

- Environmental precautions** Do not allow ANY environmental contamination. Do not discharge onto the ground or into water courses.

6.3 Methods and material for containment and cleaning up

- Spill clean up methods** Stop leak if possible without risk. DO NOT touch spilled material! Wear necessary protective equipment. Ventilate and evacuate the area. Eliminate all sources of ignition. Wear respirator if ventilation is not adequate. Use non sparking tools or equipment for clean up. Absorb spillage with non-combustible, absorbent material - sand. Do not use any basic chemical binders. Ensure that waste and contaminated materials are collected and removed from the work area as soon as possible in a suitably labelled container. In case of a large scale of spill, dyke area with sand to stop the spill spreading. Wash work area with water. In case of spills, beware of slippery floors and surfaces.

6.4 Reference to other sections

- Reference to other sections** See section 1 for emergency contact. For personal protection, see section 8. For waste disposal, see section 13.

Section 7: Handling and storage

7.1 Precautions for safe handling

- Handling** Keep away from heat, sparks and open flame. Static electricity and formation of sparks must be prevented. Do not eat, drink or smoke when using the product. Do not use contact lenses. Avoid contact with skin and eyes. Avoid inhalation of vapours. Avoid prolonged or repeated contact. Avoid forming spray/aerosol mists. Provide good ventilation. Wear personal protective equipment. Handle and open container with care. Do not mix with other chemicals. Observe good industrial hygiene practices. Keep away from any kind of soiling (in particular heavy metal ions and alkalis) because of the risk of decomposition. If necessary, use local exhaust ventilation.

7.2 Conditions for safe storage, including any incompatibilities

- Storage precautions** Prohibit ignition sources close to storage area. Material can accumulate static charges which may cause an electrical spark (ignition source). Use proper bonding and/or grounding procedures. Keep away from incompatible materials (see section 10). Store in closed, labelled containers in a cool, dry, well-ventilated area away from incompatible materials. Do not keep the container sealed. Only store in vessels with degassing valve. Suitable containers: Synthetic material coated steel. Inappropriate material for containers and conduit: Uncoated metals. Protect from humidity and keep away from water.
- Storage class** Chemical storage.

7.3 Specific end use(s)

Specific end use(s)	The identified uses for this product are detailed in Section 1.
Usage description	Use only according to directions.

Section 8: Exposure controls/Personal protection

8.1 Control parameters

Ingredient comments	No exposure limits noted for ingredient(s).
----------------------------	---

8.2 Exposure Controls

Protective equipment



Engineering measures

Facilities for handling this product should be closed system. Ensure surfaces and floors are made from non-permeable material. Provide adequate ventilation, including appropriate local extraction. Use explosion-proof ventilation equipment.

Respiratory equipment

Where risk assessment shows air-purifying respirators are appropriate a full face respirator conforming to EN143, and suitable respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as CEN (EU).

Hand protection

Change filters frequently. Use respiratory protection as specified by an industrial hygienist or other qualified professional if concentrations exceed the limits listed in Section 8. Use respiratory protective components with combined A/P filter(s) for organic vapours/particulates.

Eye protection

Where hand contact with the product may occur the use of gloves approved to relevant standards (e.g. Europe: EN374) is recommended. Gloves must be inspected prior to use. Suggested material: Fluorinated rubber. Breakthrough time: 30 - < 60 min. Minimum layer thickness: > 0.7 mm. Consult manufacturer for advice.

Other protection

Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Change gloves regularly. Selection of the glove material depends on consideration of the penetration times, rates of diffusion and degradation, and concentration specific to the workplace.

Hygiene measures

Wear safety goggles or face shield to prevent any possibility of eye contact. Use equipment for eye protection tested and approved under appropriate government standards such as EN 166(EU).

Process conditions

Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist. The selected clothing must satisfy the European norm standard EN 943.

Handle in accordance with good industrial hygiene and safety practice. Wash promptly if skin becomes wet or contaminated.

Ensure that eye flushing systems are located close by in the work place.

Section 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance	Liquid.
Colour	Transparent.
Odour	Characteristic.
Odour threshold - lower	No information available.
Odour threshold - upper	No information available.
pH-Value, Conc. Solution	No information available.
pH-Value, Diluted solution	No information available.

Melting point	No information available.
Initial boiling point and boiling range	No information available.
Flash point	> 100.00 °C
Evaporation rate	No information available.
Flammability state	No information available.
Flammability limit - lower(%)	4 %(V) Hydrogen.
Flammability limit - upper(%)	74 %(V) Hydrogen.
Vapour pressure	< 100 hPa at 20 °C.
Vapour density (air=1)	No information available.
Relative density	0.98 g/cm ³ at 23 °C. (Method: DIN 53479).
Bulk density	No information available.
Solubility	Insoluble in water.
Decomposition temperature	No information available.
Partition coefficient; n-Octanol/Water	No information available.
Auto ignition temperature (°C)	400 °C (Hydrogen).
Viscosity	Viscosity, dynamic: 650 mPa.s at 23 °C. (Brookfield HBTD).
Explosive properties	Not classified as explosive.
Oxidising properties	No information available.

9.2 Other information

Molecular weight	No information available.
Volatile organic compound	No information available.
Other information	None noted.

Section 10: Stability and reactivity

10.1 Reactivity

Reactivity	Stable under recommended transport and storage conditions and under recommended use.
-------------------	--

10.2 Chemical stability

Stability	Stable under normal temperature conditions and recommended use.
------------------	---

10.3 Possibility of hazardous reactions

Hazardous reactions	Evolves hydrogen on contact with acids, alkalis, alcohols, powdered metals or metal oxides. Violent exothermic reaction with (some) bases. Keep away from any kind of soiling (in particular heavy metal ions and alkalis) because of the risk of decomposition.
Hazardous polymerisation Polymerisation description	Hazardous polymerisation will not occur. Unknown.

10.4 Conditions to Avoid

Conditions to avoid	Temperatures above 50 degrees Celsius. Heat, sparks, open flames, temperature extremes and direct sunlight. Protect from humidity and keep away from water.
----------------------------	---

10.5 Incompatible materials

Materials to avoid Avoid contact with acids. Alkalis. Alcohols. Metal oxides. Aldehydes. Powdered metals. Avoid oxidising agents.

10.6 Hazardous decomposition products

Hazardous decomposition products Thermal decomposition or combustion may liberate carbon oxides and other harmful gases or vapors. Decomposition products may include: Hydrogen.

Section 11: Toxicological information

11.1 Information on toxicological effects

Toxicological information No toxicological information for the overall finished product.

Acute toxicity (Oral LD50) No information available.
Acute toxicity (Dermal LD50) No information available.
Acute toxicity (Inhalation LD50) No information available.

Serious eye damage/irritation May cause temporary eye irritation.

Skin corrosion/irritation No information available.

Respiratory sensitisation No information available.
Skin sensitisation No information available.

Germ cell mutagenicity No information available.

Carcinogenicity No information available.

Specific target organ toxicity - Single exposure:
STOT - Single exposure No information available.
Specific target organ toxicity - Repeated exposure:
STOT - Repeated exposure No information available.

Inhalation No specific symptoms noted.
Ingestion No specific symptoms noted.
Skin contact No specific symptoms noted.
Eye contact May cause temporary eye irritation.
Waste management When handling waste, consideration should be made to the safety precautions applying to handling of the product.

Routes of entry No information available.
Target organs No target organs specified.

Aspiration hazards: No information available.
Reproductive toxicity: No information available.

Section 12: Ecological information

12.1 Toxicity

Acute toxicity - Fish No information available.
Acute toxicity - Aquatic invertebrates No information available.
Acute toxicity - Aquatic plants No information available.
Acute toxicity - Microorganisms No information available.
Chronic toxicity - Fish No information available.
Chronic toxicity - Aquatic invertebrates No information available.
Chronic toxicity - Aquatic plants No information available.
Chronic toxicity - Microorganisms No information available.
Ecotoxicity No Ecological information on the finished product.
Eco toxicological information No ecological toxicity available on the overall finished product.

12.2 Persistence and degradability

Degradability	The product is insoluble and floats on water. May be separated mechanically in wastewater plants.
Biological oxygen demand	No information available.
Chemical oxygen demand	No information available.

12.3 Bioaccumulative potential

Bioaccumulative potential	Does not bioaccumulate.
Bioaccumulation factor	No information available.
Partition coefficient; n-Octanol/Water	No information available.

12.4 Mobility in soil

Mobility	After release, adsorbs onto soil.
-----------------	-----------------------------------

12.5 Results of PBT and vPvB assessment

Results of PBT and vPvB assessment	Product is not identified as PBT or vPvB.
---	---

12.6 Other adverse effects

Other adverse effects	No information available.
------------------------------	---------------------------

Section 13: Disposal considerations

Waste management	When handling waste, consideration should be made to the safety precautions applying to handling of the product.
-------------------------	--

13.1 Waste treatment methods

Disposal methods	Dispose of waste and residues in accordance with local authority requirements, and in accordance with all local, national and international regulations. For waste disposal, use a licensed industrial waste disposal agent.
-------------------------	--

Section 14: Transport information

14.1 UN number

UN no. (ADR)	Not applicable.
UN no. (IMDG)	Not applicable.
UN no. (IATA)	Not applicable.

14.2 UN proper shipping name

ADR proper shipping name	Not applicable.
IMDG proper shipping name	Not applicable.
IATA proper shipping name	Not applicable.

14.3 Transport hazard class(es)

ADR class	Not applicable.
IMDG class	Not applicable.
IATA class	Not applicable.

Transport labels	Not applicable
-------------------------	----------------

14.4 Packing group

ADR/RID/ADN packing group	Not applicable.
IMDG packing group	Not applicable.
IATA packing group	Not applicable.

14.5 Environmental hazards

ADR	No
IMDG	No

IATA No

14.6 Special precautions for user

EMS Not applicable.
Emergency action code Not applicable.
Hazard no. (ADR) Not applicable.
Tunnel restriction code Not applicable.

14.7 Transport in bulk according to annex II of MARPOL73/78 and the IBC code

Not applicable.

Section 15: Regulatory information

15.1 Safety, health and environmental regulations/Legislation specific for the substance or mixture

EU legislation Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments. The UN Globally Harmonized System (GHS) Safety Data Sheet format (Annex IV) is implemented as Annex II of REACH EU No 453/2010 of 20th May 2010 amending regulation (EC) No 1907/2006.

Approved code of practice Workplace Exposure Limits Guidance Note EH40/2005.

Chemical safety assessment No chemical safety assessment has been carried out.

Section 16: Other information

General information This Safety Data Sheet is in accordance with Reach Regulation (EC) No 453/2010.
Revision comments This is a first issue.
Revision date 22 February 2018
Revision 1
Safety data sheet status Approved.

Hazard statements in full

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.