SAFETY DATA SHEET MATT BLACK 496-782-0001

RS REACH MSDS Date 01/01/08

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND COMPANY/UNDERTAKING

PRODUCT NAME MATT BLACK 496-782-0001

PRODUCT NO.

Supplier: RS Components Ltd,
Birchington Road,
Corby, Northants,

NN17 9RS,

Tel: +44 (0) 1536 402888 (8am to 8pm)

Fax: +44 (0) 1536 401588

Email: technical.help@rs-components.com

2 HAZARDS IDENTIFICATION

Extremely flammable. Repeated exposure may cause skin dryness or cracking. Vapours may cause drowsiness and dizziness. Irritating to

eyes.

CLASSIFICATION Xi;R36. F+;R12. R66, R67.

3 COMPOSITION/INFORMATION ON INGREDIENTS

EC No.	CAS-No.	Content	Classification
202-436-9	95-63-6	< 1%	R10 Xn;R20 Xi;R36/37/38 N;R51/53
203-539-1	107-98-2	1-5%	R10
203-905-0	111-76-2	1-5%	Xn;R20/21/22 Xi;R36/38
203-603-9	108-65-6	1-5%	R10 Xi;R36
200-662-2	67-64-1	30-60%	F;R11 Xi;R36 R66 R67
203-448-7	106-97-8	10-30%	F+;R12
200-857-2	75-28-5	5-10%	F+;R12
203-604-4	108-67-8	< 1%	R10 Xi;R37 N;R51/53
201-297-1	80-62-6	< 1%	F;R11 R43 Xi;R37/38
200-827-9	74-98-6	10-30%	F+;R12
	64742-95-6	1-5%	Xn;R65. Xi;R37. N;R51/53. R10,R66,R67.
215-535-7	1330-20-7	5-10%	R10 Xn;R20/21 Xi;R38
	202-436-9 203-539-1 203-905-0 203-603-9 200-662-2 203-448-7 200-857-2 203-604-4 201-297-1 200-827-9	202-436-9 95-63-6 203-539-1 107-98-2 203-905-0 111-76-2 203-603-9 108-65-6 200-662-2 67-64-1 203-448-7 106-97-8 200-857-2 75-28-5 203-604-4 108-67-8 201-297-1 80-62-6 200-827-9 74-98-6 64742-95-6	202-436-9 95-63-6 < 1%

The Full Text for all R-Phrases are Displayed in Section 16

4 FIRST-AID MEASURES

GENERAL INFORMATION

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

INHALATION

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

DO NOT INDUCE VOMITING! Rinse mouth thoroughly with water and give large amounts of milk or water to people not unconscious. Get medical attention if any discomfort continues.

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

MATT BLACK 496-782-0001

SPECIAL FIRE FIGHTING PROCEDURES

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Wear necessary protective equipment. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Let evaporate. Keep out of confined spaces because of explosion risk. If leakage cannot be stopped, evacuate area.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

STORAGE PRECAUTIONS

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	LT - ppm	LT - mg/m3	ST - ppm	ST - mg/m3
1-METHOXY-2-PROPANOL	WEL	100 ppm(Sk)	375 mg/m3(Sk)	150 ppm(Sk)	560 mg/m3(Sk)
2-BUTOXYETHANOL	WEL	25 ppm(Sk)		50 ppm(Sk)	
2-METHOXY-1-METHYLETHYL ACETATE	WEL	50 ppm(Sk)	274 mg/m3(Sk)	100 ppm(Sk)	548 mg/m3(Sk)
ACETONE	WEL	500 ppm	1210 mg/m3	1500 ppm	3620 mg/m3
BUTANE	WEL	600 ppm	1450 mg/m3	750 ppm	1810 mg/m3
ISOBUTANE	WEL	800 ppm		800 ppm	
METHYL METHACRYLATE	WEL	50 ppm	208 mg/m3	100 ppm	416 mg/m3
PROPANE		Asphyxiating	Asphyxiating	Asphyxiating	Asphyxiating
XYLENE	WEL	50 ppm(Sk)	220 mg/m3(Sk)	100 ppm(Sk)	441 mg/m3(Sk)

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

PROTECTIVE EQUIPMENT





ENGINEERING MEASURES

Provide adequate general and local exhaust ventilation.

RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the Recommended Workplace Exposure Limit. Use chemical cartridge protection with appropriate cartridge.

HAND PROTECTION

Use protective gloves.

EYE PROTECTION

Use approved safety goggles or face shield.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

MATT BLACK 496-782-0001

APPEARANCE Aerosol
COLOUR Black

ODOUR Characteristic
SOLUBILITY Insoluble in water

FLAMMABILITY LIMIT - LOWER(%) 0.8 FLAMMABILITY LIMIT - UPPER(%) 13.0

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.

HAZARDOUS DECOMPOSITION PRODUCTS

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO2).

11 TOXICOLOGICAL INFORMATION

INHALATION

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system. Irritating to respiratory system.

INGESTION

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

SKIN CONTACT

Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin. May cause cracking of skin, and eczema. May cause allergic contact eczema. May cause sensitisation by skin contact. Irritating to skin.

EYE CONTACT

Irritating to eyes. May cause chemical eye burns.

ROUTE OF ENTRY

Inhalation. Skin and/or eye contact.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION



UK ROAD CLASS 2

PROPER SHIPPING NAME AEROSOLS

UN NO. ROAD 1950 UK ROAD PACK GR. N/A

ADR CLASS NO. 2 ADR CLASS Class 2: Gases
ADR PACK GROUP N/A ADR LABEL NO. 2.1

 CEFIC TEC(R) NO.
 20G5F
 RID CLASS NO.
 2

 RID PACK GROUP
 N/A
 UN NO. SEA
 1950

IMDG CLASS2.1IMDG PACK GR.Not ApplicableEMSF-D, S-UMFAGSee GuideMARINE POLLUTANTNo.UN NO. AIR1950

MATT BLACK 496-782-0001

AIR CLASS 2.1 AIR PACK GR. N/A

15 REGULATORY INFORMATION

LABELLING





ant Extremely Flammable

RISK PHRASES

R12 Extremely flammable.

R36 Irritating to eyes.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

S16 Keep away from sources of ignition - No smoking.

S23 Do not breathe vapour/spray.

S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical

advice.

S37 Wear suitable gloves.

S2 Keep out of the reach of children
S51 Use only in well-ventilated areas.

UK REGULATORY REFERENCES

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

The Control of Substances Hazardous to Health Regulations 2002.

STATUTORY INSTRUMENTS

The Control of Substances Hazardous to Health Regulations 2002.

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

Introduction to Local Exhaust Ventilation HS(G)37.

CHIP for everyone HSG(108).

16 OTHER INFORMATION

REVISION DATE 10/01/2008

REV. NO./REPL. SDS GENERATED 6

MATT BLACK 496-782-0001

RISK PHRASES IN FULL

R10 Flammable.
R11 Highly flammable.
R12 Extremely flammable.
R20 Harmful by inhalation.

R20/21 Harmful by inhalation and in contact with skin.

R20/21/22 Harmful by inhalation, in contact with skin and if swallowed.

R36 Irritating to eyes.

R36/37/38 Irritating to eyes, respiratory system and skin.

R36/38 Irritating to eyes and skin.
R37 Irritating to respiratory system.

R37/38 Irritating to respiratory system and skin.

R38 Irritating to skin.

R43 May cause sensitisation by skin contact.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.