

SAFETY DATA SHEET

Aluminium AISi10Mg

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name

Aluminium AISi10Mg

Other names / Synonyms

Document No.: H-5800-0947-02-A_EN

Product no.

A-5771-0403

1.2. Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture

Metal powder for additive layer manufacture

Uses advised against

None known.

1.3. Details of the supplier of the safety data sheet

Company and address

Renishaw plc

New Mills

Wotton-under-Edge,

GL12 8JR, Gloucestershire,

United Kingdom

+44 (0) 1453 524524

www.renishaw.com

E-mail

msds@renishaw.com

Revision

23/02/2023

SDS Version

1.0

1.4. Emergency telephone number

The National Poisons Information Centre (NPIC)

Public: +353 (0) 1 809 2166 (7 days a week, 8am- 10pm)

Healthcare professionals: +353 (0) 1 809 2566 (24 h service)

See also section 4 "First aid measures"

Emergency contact from supplier: +44 (0) 1453 524524 (UK office hours 08:00 to 17:00 UTC Monday to Thursday, 08:00 to 16:00 Friday)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Not classified according to Regulation (EC) No. 1272/2008 (CLP).

2.2. Label elements

Hazard pictogram(s)

Not applicable.

Signal word

Not applicable.

Hazard statement(s)

Not applicable.

Safety statement(s)

General

-

Prevention

-

According to EC-Regulation 1907/2006 (REACH), annex II, including changes implemented by EC-Regulation 2020/878

Response

-

Storage

-

Disposal

-

Hazardous substances

None known.

Additional labelling

EUH210, Safety data sheet available on request.

2.3. Other hazards

Additional warnings

May form combustible dust concentrations in air.

This mixture/product does not contain any substances considered to meet the criteria classifying them as PBT and/or vPvB.

This product does not contain any substances considered to be endocrine disruptors in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605.

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable. This product is a mixture.

3.2. Mixtures

Product/substance	Identifiers	% w/w	Classification	Note
Aluminium powder (stabilised)	CAS No.: 7429-90-5 EC No.: 231-072-3 REACH: Index No.:	87.3%	Flam. Sol. 1, H228 Water-react. 2, H261	
Silicon	CAS No.: 7440-21-3 EC No.: 231-130-8 REACH: Index No.:	11%		

See full text of H-phrases in section 16. Occupational exposure limits are listed in section 8, if these are available.

Other information

-

Aluminium powder (stabilised)

Note T: This substance may be marketed in a form which does not have the physical hazards as indicated by the classification in the entry in Part 3. If the results of the relevant method or methods in accordance with Part 2 of Annex I of this Regulation show that the specific form of substance marketed does not exhibit this physical property or these physical hazards, the substance shall be classified in accordance with the result or results of this test or these tests. Relevant information, including reference to the relevant test method(s) shall be included in the safety data sheet.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

In the case of accident: Contact a doctor or casualty department – take the label or this safety data sheet.

Contact a doctor if in doubt about the injured person's condition or if the symptoms persist. Never give an unconscious person water or other drink.

Inhalation

Upon breathing difficulties or irritation of the respiratory tract: Bring the person into fresh air and stay with him/her.

Skin contact

Upon irritation: rinse with water. In the event of continued irritation, seek medical assistance.

Eye contact

Upon irritation of the eye: Remove contact lenses. Flush eyes with plenty of water or salt water (20-30 °C) and continue until irritation stops.

According to EC-Regulation 1907/2006 (REACH), annex II, including changes implemented by EC-Regulation 2020/878

Ingestion

If the person is conscious, rinse the mouth with water and stay with the person. Never give the person anything to drink.

In case of malaise, seek medical advice immediately and bring the safety data sheet or label from the product. Do not induce vomiting, unless recommended by the doctor. Have the person lean forward with head down to avoid inhalation of or choking on vomited material.

Burns

Not applicable.

4.2. Most important symptoms and effects, both acute and delayed

None known.

4.3. Indication of any immediate medical attention and special treatment needed

None known.

Information to medics

Bring this safety data sheet or the label from this product.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media: Use class D extinguishing agents on dust, fines or molten metal.

Unsuitable extinguishing media: Water, foam, halogenated extinguishing agents.

5.2. Special hazards arising from the substance or mixture

Fire will result in dense smoke. Exposure to combustion products may harm your health. Closed containers, which are exposed to fire, should be cooled with water. Do not allow fire-extinguishing water to enter the sewage system and nearby surface waters.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and protective clothing to prevent contact. Upon direct exposure contact the National Poisons Information Centre (NPIC) on +353 (0) 1 809 256 (24 h service) in order to obtain further advice.

Fire fighters should wear appropriate personal protective equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Dust deposits should not be allowed to accumulate on surfaces, as these may form an explosive mixture if they are released into the atmosphere in sufficient concentration.

Evacuate surrounding areas.

Eliminate all ignition sources.

Ventilate the area.

Wear appropriate personal protective equipment (see section 8).

6.2. Environmental precautions

Avoid discharge to lakes, streams, sewers, etc.

6.3. Methods and material for containment and cleaning up

Collect spills carefully. Moist the material with water in order to prevent the formation and propagation of dust.

Wherever possible cleaning should be performed with normal cleaning agents. Avoid use of solvents.

Use spark-proof tools and explosion-proof equipment.

Avoid dust generation.

Ensure that waste and contaminated materials are collected and removed from the work area as soon as possible in a suitably labelled container.

6.4. Reference to other sections

See section 13 "Disposal considerations" on handling of waste.

See section 8 "Exposure controls/personal protection" for protective measures.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Routine housekeeping should be instituted to ensure that dusts do not accumulate on surfaces.

Smoking, drinking and consumption of food is not allowed in the work area.

See section 8 "Exposure controls/personal protection" for information on personal protection.

Take precautionary measures against static discharges.

7.2. Conditions for safe storage, including any incompatibilities

Avoid the suspension of dust in the air.

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

According to EC-Regulation 1907/2006 (REACH), annex II, including changes implemented by EC-Regulation 2020/878

Use non-sparking tools.

Recommended storage material

Always store in containers of the same material as the original container.

Storage temperature

Store in tightly closed original container in a dry, cool and well-ventilated place.

Store in accordance with local regulations.

Incompatible materials

Strong acids, strong bases, strong oxidizing agents, and strong reducing agents.

7.3. Specific end use(s)

This product should only be used for applications quoted in section 1.2.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Aluminium powder (stabilised)

Long term exposure limit (8 hours) (mg/m³): 1 (Respirable Fraction)

Silicon

Long term exposure limit (8 hours) (mg/m³): 4

2021 Code of Practice for the Safety, Health and Welfare at Work (Chemical Agents) Regulations (2001-2015) and the Safety, Health and Welfare at Work (Carcinogens) Regulations (2001-2019).

DNEL

No data available.

PNEC

No data available.

8.2. Exposure controls

Compliance with the given occupational exposure limits values should be controlled on a regular basis.

Where necessary use lighting and electrical equipment designed for use in atmospheres where flammable vapours or dusts are present, and which can direct static electricity by grounding equipment.

General recommendations

When transferring the materials, dust clouds should be kept at an absolute minimum. Handling should be slow and deliberate. The materials should be transferred from one container to another using a non-sparking, conductive metal scoop.

When mixing the material with other dry ingredients, frictional heat should be avoided. The best type of mixer for a dry mixing operation is one that contains no moving parts, but rather affects a tumbling action, such as a conical blender. Introduction of an inert atmosphere in the blender is highly recommended since dust clouds are generated. All equipment must be well grounded.

Smoking, drinking and consumption of food is not allowed in the work area.

Exposure scenarios

There are no exposure scenarios implemented for this product.

Exposure limits

Professional users are subjected to the legally set maximum concentrations for occupational exposure. See occupational hygiene limit values above.

Appropriate technical measures

Airborne gas and dust concentrations must be kept at a minimum and below current limit values (see above).

Installation of a local exhaust system if normal air flow in the work room is not sufficient is recommended. Ensure emergency eyewash and showers are clearly marked.

Hygiene measures

Wash hands after use.

Measures to avoid environmental exposure

No specific requirements.

Individual protection measures, such as personal protective equipment


Generally

Use only CE marked protective equipment.

Respiratory Equipment


According to EC-Regulation 1907/2006 (REACH), annex II, including changes implemented by EC-Regulation 2020/878

Type	Class	Colour	Standards
SL	P3	White	EN149




Skin protection

Recommended	Type/Category	Standards
Protective footwear	Protective footwear	
Dedicated work clothing should be worn. Wear a protective suit in the event of prolonged periods of work with the product.	-	-




Hand protection

Material	Glove thickness (mm)	Breakthrough time (min.)	Standards
Butyl	0,3	> 480	EN374-2, EN374-3, EN388



Eye protection

Type	Standards
Safety glasses with side shields.	EN166



SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state

Powder

Colour

Gray

Odour / Odour threshold

None

pH

Not applicable - product is a solid

Density (g/cm³)

2.67

Kinematic viscosity

Not applicable - product is a solid

Particle characteristics

Particle size: 20 - 63 µm

Phase changes

Melting point/Freezing point (°C)

No information available as testing has not been completed.

Softening point/range (waxes and pastes) (°C)

Does not apply to solids.

Boiling point (°C)

No information available as testing has not been completed.

Vapour pressure

Testing not relevant or not possible due to the nature of the product.

Relative vapour density

Does not apply to solids.

Decomposition temperature (°C)

No information available as testing has not been completed.

Data on fire and explosion hazards

Flash point (°C)

Does not apply to solids.

Flammability (°C)

Testing not relevant or not possible due to nature of the product.

Auto-ignition temperature (°C)

Testing not relevant or not possible due to nature of the product.

Lower and upper explosion limit (% v/v)

Does not apply to solids.

Solubility

Solubility in water

Insoluble

n-octanol/water coefficient

No information available as testing has not been completed.

Solubility in fat (g/L)

No information available as testing has not been completed.

9.2. Other information

Formation of explosible dust/air mixtures

Yes

Evaporation rate (n-butylacetate = 100)

Not applicable - product is a solid

Other physical and chemical parameters

No data available.

SECTION 10: Stability and reactivity

10.1. Reactivity

No data available.

10.2. Chemical stability

The product is stable under the conditions, noted in section 7 "Handling and storage".

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Avoid the suspension of dust in the air.

10.5. Incompatible materials

Strong acids, strong bases, strong oxidizing agents, and strong reducing agents.

10.6. Hazardous decomposition products

The product is not degraded when used as specified in section 1.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity

Product/substance	Silicon
Species:	Rabbit
Route of exposure:	Dermal
Test:	LD50
Result:	> 5000 mg/kg

Skin corrosion/irritation

Based on available data, the classification criteria are not met.

Serious eye damage/irritation

Based on available data, the classification criteria are not met.

Respiratory sensitisation

Based on available data, the classification criteria are not met.

Skin sensitisation

Based on available data, the classification criteria are not met.

Germ cell mutagenicity

Based on available data, the classification criteria are not met.

Carcinogenicity

Based on available data, the classification criteria are not met.

According to EC-Regulation 1907/2006 (REACH), annex II, including changes implemented by EC-Regulation 2020/878

Reproductive toxicity

Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

11.2. Information on other hazards

Long term effects

None known.

Endocrine disrupting properties

Not applicable.

Other information

None known.

Exposure to metal dusts and oxides may cause metal fume fever. Metal fume fever is a temporary flu-like condition characterized by chills, fever, muscle aches and pains, nausea, and vomiting. Typically, the symptoms appear within a few hours after exposure and subside within 2-3 days with no permanent effects.

SECTION 12: Ecological information

12.1. Toxicity

No data available.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential

Product/substance Silicon

Test method:

Potential bioaccumulation: No data available.

LogPow: 54 - 77 (25°C, pH 7 - 8)

BCF: No data available.

Other information:

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

This mixture/product does not contain any substances considered to meet the criteria classifying them as PBT and/or vPvB.

12.6. Endocrine disrupting properties

Not applicable.

12.7. Other adverse effects

None known.

SECTION 13: Disposal considerations

Waste treatment methods

Product is not covered by regulations on dangerous waste.

Commission Regulation (EU) No 1357/2014 of 18 December 2014 on waste.

EWC code

Not applicable.

Specific labelling

Not applicable.

Contaminated packing

Packaging containing residues of the product must be disposed of similarly to the product.

SECTION 14: Transport information

According to EC-Regulation 1907/2006 (REACH), annex II, including changes implemented by EC-Regulation 2020/878

	14.1 UN / ID	14.2 UN proper shipping name	14.3 Hazard class(es)	14.4 PG*	14.5 Env**	Other information:
ADR	-	-	-	-	-	-
IMDG	-	-	-	-	-	-
IATA	-	-	-	-	-	-

* Packing group

** Environmental hazards

Additional information

Not dangerous goods according to ADR, IATA and IMDG.

14.6. Special precautions for user

Not applicable.

14.7. Maritime transport in bulk according to IMO instruments

No data available.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Restrictions for application

Restricted to professional users.

Demands for specific education

No specific requirements.

SEVESO - Categories / dangerous substances

Not applicable.

Regulation on explosives precursors

Aluminium powder (stabilised) (Annex II)

Additional information

Not applicable.

Sources

Council Regulation (EC) No 2019/1148 on explosives precursors.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (CLP).

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH).

15.2. Chemical safety assessment

No

SECTION 16: Other information

Full text of H-phrases as mentioned in section 3

H228, Flammable solid.

H261, In contact with water releases flammable gases.

Abbreviations and acronyms

ADN = European Provisions concerning the International Carriage of Dangerous Goods by Inland Waterway

ADR = The European Agreement concerning the International Carriage of Dangerous Goods by Road

ATE = Acute Toxicity Estimate

BCF = Bioconcentration Factor

CAS = Chemical Abstracts Service

CE = Conformité Européenne

CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]

CSA = Chemical Safety Assessment

CSR = Chemical Safety Report

DMEL = Derived Minimal Effect Level

DNEL = Derived No Effect Level

EINECS = European Inventory of Existing Commercial chemical Substances

ES = Exposure Scenario

EUH statement = CLP-specific Hazard statement

EWC = European Waste Catalogue

GHS = Globally Harmonized System of Classification and Labelling of Chemicals

According to EC-Regulation 1907/2006 (REACH), annex II, including changes implemented by EC-Regulation 2020/878

IARC = International Agency for Research on Cancer (IARC)
IATA = International Air Transport Association
IBC = Intermediate Bulk Container
IMDG = International Maritime Dangerous Goods
LogPow = logarithm of the octanol/water partition coefficient
MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
OECD = Organisation for Economic Co-operation and Development
PBT = Persistent, Bioaccumulative and Toxic
PNEC = Predicted No Effect Concentration
RID = The Regulations concerning the International Carriage of Dangerous Goods by Rail
RRN = REACH Registration Number
SCL = A specific concentration limit
SVHC = Substances of Very High Concern
STOT-RE = Specific Target Organ Toxicity - Repeated Exposure
STOT-SE = Specific Target Organ Toxicity - Single Exposure
TWA = Time weighted average
UN = United Nations
UVBC = Unknown or variable composition, complex reaction products or of biological materials
VOC = Volatile Organic Compound
vPvB = Very Persistent and Very Bioaccumulative

Additional information

Not applicable.

The safety data sheet is validated by
EcoOnline

Other

A change (in proportion to the last essential change (first cipher in SDS version, see section 1)) is marked with a blue triangle.

The information in this safety data sheet applies only to this specific product (mentioned in section 1) and is not necessarily correct for use with other chemicals/products.

It is recommended to hand over this safety data sheet to the actual user of the product. Information in this safety data sheet cannot be used as a product specification.

Country-language: IE-en