

# Technical note

## The testing of a Renishaw SP600M scanning probe to determine three key performance characteristics

**Test report  
compiled by:** Richard Johns  
Product Marketing Engineer  
Renishaw plc

**Date:** 12<sup>th</sup> December 2001

# Test 1

## Objectives

To evaluate the performance of the SP600M in relation to scanning with different deflections, without re-calibrating the probe for those deflections.

## Method

ISO 10360-4 test.

Three different SP600 probes were tested with a stylus length of 50 mm, performing the ISO 10360-4 test at different nominal deflections (using just one calibration).

Scan speed: 5 mm/s  
Machine specification: 5+L/250 µm  
Controller: Renishaw UCC controller  
Stylus material: Ceramic

## Results *(NOTE: Raw data, i.e. no filters, have been utilised.)*

Probe serial no.	Result	Deflection (mm)				
		0.2	0.3	0.4	0.5	0.6
T37931	RMS	0.91	0.69	0.55	0.61	0.89
	Min	-2.9	-2.0	-1.9	-2.2	-2.4
	Max	2.5	2.0	1.8	1.9	3.1
	Radius Error	0.0010	0.0010	0.0008	0.0006	0.0001
T70366	RMS	0.96	0.8	0.7	0.76	1.08
	Min	-2.3	-2.1	-2.2	-2.6	-3.3
	Max	2.9	2.7	2.2	2.0	2.9
	Radius Error	0.0006	0.0009	0.0008	0.0006	0.0005
T74786	RMS	0.85	0.61	0.51	0.56	0.77
	Min	-2.2	-1.8	-1.8	-2.0	-2.8
	Max	2.3	1.8	1.4	2.2	3.0
	Radius Error	0.0009	0.0009	0.0009	0.0009	0.0006

## Conclusion

Changing the deflection of the probe, causing varying probing force, has no discernible affect upon the quality of the measurement data.

## Test 2

### Objectives

To confirm that increasing the stylus length on an SP600M does not introduce sensitivity to deflection.

### Method

ISO 10360-4 test.

An SP600 probe (serial no. T74786) was tested using different stylus lengths, performing the ISO 10360-4 test at different nominal deflections (using just one calibration).

Scan speed: 5 mm/s  
Machine specification: 5+L/250  $\mu$ m  
Controller: Renishaw UCC controller  
Stylus material: Ceramic

### Results *(NOTE: Raw data, i.e. no filters, have been utilised.)*

Stylus length	Result	Deflection (mm)			
		0.2	0.3	0.4	0.5
50 mm	RMS	0.85	0.61	0.51	0.56
	Min	-2.2	-1.8	-1.8	-2.0
	Max	2.3	1.8	1.4	2.2
	Radius Error	0.0009	0.0009	0.0009	0.0009
100 mm	RMS	1.10	0.86	0.83	1.03
	Min	-2.9	-2.4	-2.5	-2.8
	Max	3.6	2.6	3.2	2.8
	Radius Error	0.0006	0.0008	0.0006	0.0004
200 mm	RMS	1.29	1.23	1.49	1.93
	Min	-6.8	-4.3	-4.2	-5.3
	Max	6.1	4.3	8.0	8.1
	Radius Error	0.0014	0.0016	0.0015	0.0009

### Conclusion

Even with increasing stylus length, the varying deflection of the probe has no discernible affect upon the quality of the measurement data.

## Test 3

### Objectives

Investigate the SP600M's performance with increased stylus lengths.

### Method

An SP600M probe (serial no. P37381) was calibrated using different stylus lengths.

For each stylus, an ISO 10360-4 scanning test and a ring gauge test was performed.

Scan speed: 5 mm/s  
Machine specification: 5+L/250  $\mu\text{m}$   
Controller: Renishaw UCC controller  
Stylus material: Ceramic  
Data filter: Harmonic filter with a cut-off order of 60 cycles per revolution ( $\omega_c=377\text{rad/s}$ )

### Results

Stylus length	ISO scanning test		Ring gauge scans	
	Raw data span ( $\mu\text{m}$ )	Filtered data span ( $\mu\text{m}$ )	Raw data span ( $\mu\text{m}$ )	Filtered data span ( $\mu\text{m}$ )
20 mm	3.5	<b>2.2</b>	3.7	<b>1.9</b>
50 mm	2.9	<b>1.9</b>	4.3	<b>2.2</b>
100 mm	3.8	<b>2.5</b>	4.8	<b>2.6</b>
150 mm	5.1	<b>3.7</b>	6.1	<b>2.9</b>
200 mm	9.0	<b>3.7</b>	8.5	<b>3.1</b>

### Conclusion

Whilst there is a deterioration of measurement accuracy with an increase in length, the deformation is small, especially when filtered data is considered.