

# Data sheet: vacuum casting resin 8020-1

Description			Very low viscosity
Features			High elongation, high strength
Suitable for			Ideal for thin wall sections on gaskets, seals, and valves
Cured properties			Test / ISO standard where applicable
Colour		Yellow	
Transparency		Translucent	
Shore hardness	At 23 °C At 60 °C At 80 °C	50 A Not measured Not measured	868
Flexural strength		Not measured	178
Flexural modulus		Not measured	178
Tensile strength		5 N/mm <sup>2</sup>	R 527
Tensile modulus		3 N/mm <sup>2</sup>	R 527
Izod impact		Not measured	180
Yield strength		Not measured	R 527
Elongation yield		Not measured	
Elongation at break		600 %	R 527
Tear strength		11 N/mm <sup>2</sup> to 12 N/mm <sup>2</sup>	34
Thermal conductivity		0.175 W/mK	BS 874
Heat deflection temperature		Not measured	(test piece 110 mm × 12.7 mm × 6.4 mm)
Glass transition temperature		Not measured	
Processing information			Notes
Viscosity	Part A Part B	550 cPs 500 cPs	At 25 °C
Specific gravity	Part A Part B	1.03 1.12	At 25 °C
Mix ratio A:B		100:75	By weight
Mixing time		45 s to 60 s	
Resin temperature		40 °C	Heating chamber
Mould temperature		70 °C	Heating chamber
Curing temperature		70 °C	Heating chamber
Curing time in mould		120 min	
Pot life		300 s	100 g at 25 °C
Post curing process		None	
Typical shrinkage		0.2 %	

The information in this data sheet is provided for general guidance only and must not be relied upon as a definitive statement of the product's properties or suitability. Renishaw will not be liable for the consequences of any decision by you to use the product and you must conduct your own testing to determine whether or not the product is suitable for your needs.

# Handling procedure

## Casting procedure

- Shake unopened A and B component cans vigorously for 10 s to 15 s
- Pre-heat mould in oven at 70 °C
- Pre-heat unopened A and B component cans in oven at 70 °C for 2 hours, then place in oven at 40 °C to stabilise prior to use
- Weigh A and B components into separate cups, allowing for cup loss (the amount of resin left in cup A after tipping)
- Add colour pigment to cup A
- Place filled cups in the machine and attach mixing paddle to cup B
- Start vacuum pump
- Switch on mixer motor
- Wait 10 minutes after reaching maximum vacuum level before mixing
- Pour contents of cup A into cup B and mix as fast as possible without splashing
- Pour mixed resin into silicone mould and leak vacuum chamber before the end of the pot life
- Place filled mould in oven to cure resin
- For full instructions on casting procedures refer to **Vacuum Casting Technique: a guide for new users**, available at [www.renishaw.com](http://www.renishaw.com)

## Special notes

- Exact mould temperature is important
- Exact resin temperature is important
- Use no more than 1 % of total weight colour pigment

## Product information

- **Minimum shot weight**  
Minimum shot weight is 150 g.
- **Mould life**  
Mould life can be increased by using the correct Renishaw release agent and demoulding the casting immediately after curing.
- **Storage**  
Store unopened cans at > 20 °C  
Protect against frost  
Store opened cans in oven at 40 °C with caps on  
Both components are sensitive to humidity.
- **In case of crystallisation of B-component**  
Place cans in oven at 70 °C for 2 hours to 4 hours and stir resin afterwards.



Please follow the correct procedure for use in your vacuum casting system, as set out in its operating instructions.



Always follow the instructions in the Product Safety Data Sheets and always work in accordance with the safety instructions of the materials manufacturer. Safety Data Sheets can be found at [www.renishaw.com](http://www.renishaw.com).



Wear suitable respiratory protection, safety gloves and safety goggles during the entire filling procedure in accordance with the Product Safety Data Sheets.

