

# Bondmaster Double Bubble Two Part Epoxy Resin Technical Information Sheet



Woodside Road, Eastleigh  
Hampshire SO50 4EX  
Tel: 023 8061 9822  
Fax: 023 8065 2270

## Description:

Bondmaster Double Bubble (also known as Mix & Fix) will bond to a wide variety of materials (i.e. wood, metal, plastic and ceramic) and cures rapidly to give handling strength in approximately 5 minutes. Packed into a handy sachet, and supplied complete with a mixing stick and pallet, these features provide an adhesive suitable for the rapid assembly of small components or for fast and effective repair work.

## Physical Properties:

	<u>Part A - Resin</u>	<u>Part B - Hardener</u>	<u>Mixed</u>
Colour	Clear	Clear	Clear
Viscosity (mPa.s)	60,000	12,000	35,000
Specific Gravity	1.2	1.13	1.16
Mix Ratio	- By Weight - By Volume	100:94 1:1	Gap Fill (on a vertical surface) < 1 mm

Generally the recommended service temperature range for this product is -55 to +100°C. However experience has shown that higher temperatures, of around 200°C, may be endured for short periods providing the adhesive is not unduly stressed.

## Typical Performance:

<u>Cure Speed</u>	<u>Usable Life</u>	<u>Handling Strength</u>	<u>Working Strength</u>	<u>Full Strength</u>	The cure speed of 2 part epoxy resins is generally affected by the ambient temperature. A fall of 8°C will roughly double the cure time; a rise of 8°C will tend to halve it.
- at 23°C	3 min	5 min	30 mins.	24 hrs.	
- at 60°C	—	—	2 mins.	30 mins.	
Lap Shear Strength	9 (Steel)		On <b>Composites</b> this adhesive is capable of strengths similar to that achieved on steel but in most cases delamination on the composite will occur before this load is reached. On <b>Aluminium &amp; Copper</b> alloys the modulus and thickness of the metal will define the ultimate bond strength achieved.		

## Storage :

When stored in the original unopened containers at 5-25°C, the shelf life of this product is 24 months from the date of despatch from Bondmaster.

## Handling:

Full information can be obtained from the Material Safety Data Sheet (M.S.D.S.). Users are reminded that all materials, whether innocuous or not, should be handled according to the principles of good industrial hygiene.

## Directions for Use:

Thoroughly mix Resin (A) and Hardener(B) in the correct proportion. Do not mix more material than can be applied during the 'usable life' of the product. Surfaces should be clean, dry and grease free before applying the adhesive. Where maximum strength is required then the surfaces should be shot blasted, or lightly abraded, in the presence of Bondmaster SIP. Bondmaster Double Bubble can be cured at temperatures down to 0°C but care must be taken to ensure the surfaces are not coated with condensation.

The information given and the recommendations made herein are based on our experience and are believed to be accurate. No guarantee as to, or responsibility for, their accuracy can be given or accepted, however, and no statement herein is to be treated as a representation or warranty. In every case we urge and recommend that purchasers, before using any product, make their own tests to determine, to their own satisfaction, its suitability for their particular purposes under their own operating conditions.

15/04/04