



# Renishaw modulated optical probe transmission technology

Renishaw's modulated transmission technology is an optical transmission method that replaces Renishaw's original transmission protocol, which is now referred to as 'Legacy' transmission or 'Legacy mode'.

Modulated transmission is used across the current range of Renishaw optical workpiece inspection probes as well as the OTS contact tool setter. The effective range of modulated optical transmission is up to 6 m and relies on line-of-sight, although it can benefit from reflections.

## System components

Modulated transmission is used on the OMP, OLP and OTS ranges of probes, which utilise either an optical machine interface (OMI-2, OMI-2T, OMM-2C) or a combination of optical machine module receiver (OMM-2) and a separate machine interface (OSI-D or OSI). The separate interface allows two OMM-2s to be used, providing a solution for large machine tools or where line-of-sight difficulties exist.

Modulated transmission allows multiple optical probes to be used in succession, on a single machine tool. A common application of this uses one workpiece inspection probe and two OTS probes on a twin pallet machining centre, one OTS equipping each pallet.




Figure 1: OMP40-2 workpiece inspection probe with optical transmission

Figure 2: OMI-2 optical machine interface

## Modulated transmission protocol

Optical transmission signals between the probe and receiver are coded into a series of flashes. Renishaw products use a modulated transmission protocol, which is robust and impervious to interference from other infrared light sources.

When a workpiece inspection probe is taken from a tool carousel and fitted into a spindle it can be activated by the interface using a start code. Renishaw's modulated transmission protocol prevents optical interference turning on the probe and wasting battery life.

The code allows separate activation signals for multiple probes using a single interface. For example, a machine tool with automatic pallet changing could be equipped with an optical inspection probe and two optical tool setting probes (OTS), one on each pallet. Such a configuration ensures tool setting and broken tool detection are always available.

Renishaw modulated transmission protocol is an extremely robust system. Under testing and in use it has proven to be highly immune to interference from sunlight and fluorescent light sources. The coding mechanism ensures it is extremely unlikely that a fluorescent light source will emulate a probe signal, while further detection and rejection coding methods provide additional protection.




Figure 3: OMM-2 with OSI shown with an optional second OMM-2

## Effective range of modulated transmission

Modulated optical transmission systems are directional, with the probe and receiver having defined windows of operation as shown in figure 4. Maximum range is achieved by fitting the system components to face along the optical centre-line.

The size of probe can have an effect on its transmission range. Smaller Renishaw probes, designated by the figures 40 or 400 in their model name, have fewer iREDs which results in a lower intensity of infrared light emission and reduced range. However, as the smaller probes are intended for use on smaller machine tools, the required transmission range is also correspondingly reduced.




Figure 4: transmission plots of an OMP60 probe and OMI-2/OMI-2T interfaces

## Summary

Renishaw modulated transmission technology produces a highly effective and robust communication system to enable interference-free wireless inspection probing. It is available on a wide range of workpiece inspection and tool setting probes, providing a transmission solution for all small-to-medium sized machine tools.

[www.renishaw.com/machinetool](http://www.renishaw.com/machinetool)



#renishaw

+44 (0) 1453 524 524

uk@renishaw.com

© 2024 Renishaw plc. All rights reserved. RENISHAW® and the probe symbol are registered trade marks of Renishaw plc. Renishaw product names, designations and the mark 'apply innovation' are trade marks of Renishaw plc or its subsidiaries. Other brand, product or company names are trade marks of their respective owners. Renishaw plc. Registered in England and Wales. Company no: 1106260. Registered office: New Mills, Wotton-under-Edge, Glos, GL12 8JR, UK.

WHILE CONSIDERABLE EFFORT WAS MADE TO VERIFY THE ACCURACY OF THIS DOCUMENT AT PUBLICATION, ALL WARRANTIES, CONDITIONS, REPRESENTATIONS AND LIABILITY, HOWSOEVER ARISING, ARE EXCLUDED TO THE EXTENT PERMITTED BY LAW.

Part no. H-5650-2042-02-A